RPM® Dimensions and Operating Instructions


Seat


	Seat Height*	Seat Depth	Seat Width	Seat Pan Angle	Seat Back/ Seat Pan Angle	Foward Tilt
BIFMA G1-200	2 Ergonomic Guidel	ines:				
	15" - 19.9" May use multiple cylinders	16.2" - 16.9"	17.7" min.	0° - 4° rearward	90° - 115°	
Basic	15" - 233/4"*	17.5"	$20^{1}/2''$	2°	93° - 109°	3°
Advanced	15" - 23 3/4"*	16.5" - 18.5"	201/2"	2°	93° - 109°	3°
High Task	231/2" - 311/4"*	see basic and advanced	201/2"	2°	93° - 109°	3°

Back

	Backrest	Lumbar Support Height	Lumbar Support Width	Lumbar Support Center Ht.	Seat Back Width	
BIFMA Stds.		5.9" - 9.8"	14.2" min.	5.9" - 9.8"	14.2" min.	
Basic	yes	5.9" - 9.9"	17"	8"	19"	
Advanced	yes	5.9" - 9.9"	17"	8"	19"	
High Task	ves	5.9" - 9.9"	17"	8"	19"	

			Basic	Advanced	High Task	Side
Α	overall height		37 1/8" - 45 5/8"	37 1/8" - 45 5/8"	433/4"-51"	321/2"
В	overall width		27"	27"	27"	22"
С	overall depth		21 1/4"	21 1/4"	21 1/4"	231/2"
D	arm height (from floor)	Fixed High Performance	24 ⁷ /8" - 29 ³ /8" 23 ³ /4" - 31 ¹ /2"	24 ⁷ /8" - 29 ³ /8" 23 ³ /4" - 31 ¹ /2"	32 ½" - 39 ½" 31" - 42"	25"
Ε	arm height (from seat)	Fixed High Performance	8 ³ / ₈ " 7 ¹ / ₄ " - 10 ¹ / ₂ "	8 ³ / ₈ " 7 ¹ / ₄ "-10 ¹ / ₂ "	8 ³ / ₈ " 7 ¹ / ₄ "-10 ¹ / ₂ "	73/4"
F	recline range		25°	25°	25°	n/a
G	base diameter		27"	27"	27"	221/2" wide
	footring (height: 9	9" - 18")			20" dia.	
Н	weight (with fixed ar	rms)	44 lbs.	44 lbs.	51 lbs.	28 lbs.





(Measurements of arm chairs, advanced control with pneumatic seat height adjustment, in inches)

Arm Dimensions	Height from the Seat Reference Point	(at the innermost	Width between Arms (measured at the inside of the arm support)		Slide (to the front or back of the chair)
Fixed arms	83/8"	16½"-19" (2½" range)	20 ³ / ₄ "-22 ³ / ₄ " (2" range)	NA	NA
High performance arms on Advanced Control chair	7 ¹ /4"-10 ¹ /2" (3 ¹ /4" range)	17 ³ / ₄ "-19 ³ / ₄ " (2" range)	20"-22" (2" range)	±15°, 30° total (3 fixed positions)	1" range
High performance arms on Basic Control chair	7 ¹ /4"-10 ¹ /2" (3 ¹ /4" range)	17 ³ / ₄ "-19 ³ / ₄ " (2" range)	20"-22" (2" range)	±15°, 30° total (3 fixed positions)	NA