



SLOT A

SLOT B

NOTE:


- Weight capacity is 20 lbs. MAX.
- WM45/Trough length is made to order at 305.00mm (12") MIN. to 1829.00mm (72") MAX.

1




Measure trough length. Install the (2) WM46/End cap to both sides of WM46/Trough.

2




Secure the WM46/End cap with (2) flat-head screws on each side.

TABLE OF CONTENTS:



.....2X WM46/Bracket



.....1X WM46/Trough



.....2X WM46/End cap




.....4X 3/4"
Pan-head screw




.....4X 9/16"
Flat-head screw

3




Determine the position and location of the part under the work surface. Mark the mounting holes by using the trough length and adding 5/8" on both sides. Install the (2) WM46/Brackets with the pan-head mounting screws.

4




Determine the height/depth needed for cables use slot A or slot B.

5




Hook the mounting pin to the desired rear mounting slot.

6




Slide the trough forward to hook the mounting pin to the corresponding front mounting slot.

7 (OPTIONAL)



Snap off end cap tab cover with cutting pliers.

8



When breaking off the tab please ensure that there are no sharp edges left by filing them down carefully.